

Ordering Information



For the detailed listing of country and product specific approvals, refer to the *Approvals Quick Reference Guide* (108M1756) available from Bently.com.

200150-AA-BB

General Purpose Trendmaster 2000 or Trendmaster Pro Accelerometer

200155-AA-BB

Low Frequency Trendmaster Pro Accelerometer

200157-AA-BB

Enveloping Trendmaster Pro Accelerometer

Refer to Table 6 for detailed specifications.

A: Mounting Stud Option

00	No mounting stud provided
01	3/8-24 thread, 2 adhesive mount frames with adhesive
02	3/8-24 to 3/8-24 UNF 1-3/8 inch hex plate stud
03	3/8-24 to 1/2-20 UNF 1-3/8 inch hex plate stud
04	3/8-24 to 1/4 NPT 1-3/8 inch hex plate stud
05	3/8-24 to 1/4-28 UNF 1-3/8 inch hex plate stud
06	3/8-24 to 1/4 NPT, 3/4 inch hex stud
07	3/8-24 to 3/8 NPT, 3/4 inch hex stud

08	3/8-24 to 1/2 NPT 1 inch hex stud
09	3/8-24 to 3/4 NPT, 1-1/4 inch hex stud
10	3/8-24 to 1 NPT, 1-3/8 inch hex stud
11	3/8-24 to 1-1/4 NPT, 1-3/4 inch hex stud
12	3/8-24 to 1/4-20 UNC, 3/4 inch hex stud
13	3/8-24 to 5/16-18 UNC, 3/4 inch hex stud
14	3/8-24 to 3/8-24 UNF, 3/4 inch hex stud
15	3/8-24 to 3/8-16 UNC, 3/4 inch hex stud
16	3/8-24 to 1/2-13 UNC, 3/4 inch hex stud
17	3/8-24 to 3/8-16 UNC 1-3/8 inch hex plate stud
18	3/8-24 to M8x1 1-3/8 inch hex plate stud
19	Quick-Set XDCR adapter, 1-inch hex stud
20	3/8-24 thread, 1 magnetic mount base
21	3/8-24 outer diameter to M6x1 inner diameter 1-3/8 inch hex plate stud
22	3/8-24 to M8x1.25 1-3/8 inch hex plate stud
23	3/8-24 to M16x2.0 1-3/8 inch hex plate stud

B: Approvals

05	Multiple Approvals (CSA, ATEX, and IECEx)
-----------	---



Adhesive studs (Options **01** and **20**) are sold in kits containing frames to hold the studs to the substrate while the adhesive cures. The kit also contains provides a scouring pad and alcohol wipe to prepare the mounting surface and a packet of acrylic adhesive and materials to mix the two components.



Using adhesives and magnetic mounts attenuates high frequency signals that may be present.

200151-AA-BB-CC

Accelerometer Interface Standard Cable, Connectors on Both Ends

A: Cable Length

20	2.0 meters
40	4.0 meters
60	6.0 meters

B: Armor Option

02	Blue cable without armor
03	Blue cable with armor

C: Coupling Nut

00	Standard coupling nut (see Figure 9)
02	Nylon coupling nut
10	Enhanced coupling nut. This option provides a better grip for tightening the cable to the accelerometer and is provided on both ends of the cable (see Figure 11).

200152-AA-BB

Accelerometer Interface Standard Cable, Connector on Accelerometer End Only

A: Cable Length

04	4.0 meters
15	15 meters
25	25 meters

B: Coupling Nut

00	Standard coupling nut (see Figure 10)
10	Enhanced coupling nut. This option provides a better grip for tightening the cable to the accelerometer and is provided on the accelerometer end only (see Figure 12).